

BLS SRL via dei Giovi, 41 20032 Cormano (MI) - Italy t/f +39 0239310212 / 0266200473 info@blsgroup.com - www.blsgroup.com

BLS SGE46 *REUSABLE HALF MASKS RESPIRATORS WITH UNIVERSAL CONNECTION EN148-1*

BLS SGE46 single connection reusable respirators are flexible silicone half masks that combined with standard EN148-1 threaded filters (universal for all respiratory protection devices) can protect against gases / vapors and toxic particulates.

HARNESS

Fixed on 2 points directly on the rigid body of the mask allowing to distribute the weight of the respirator evenly without leaving face marks.

> UNIVERSAL CONNECTION Standard thread connection according to EN 148-1, universal among all respiratory protection devices.

> > R 19/09/19











FACE PIECE

The face piece made of silicone rubber is designed to universally adapt to all face sizes giving a better comfort and perfect fit.



p 2/3

BLS SGE46 REUSABLE HALF MASKS RESPIRATORS WITH UNIVERSAL CONNECTION EN148-1

MATERIALS

FACE PIECE	Silicone
VALVES AND FILTERS HOLDER	Polyamide (PA)
HARNESS HOLDER	Polypropylene (PP)
HARNESS	Polyester and coated rubber
HEADPIECE	Polyethylene (PE)

All components in direct contact with user's face are LATEX FREE

TECHNICAL DATA

MODEL	FACE PIECE	CONNECTION	NPF (particle and combined filter)	NPF (gas filter)
SGE46	Silicone	EN148-1 (Universal)	12*TLV (P2) 48*TLV (P3)	50*TLV
(TLV) Threshold	Limit Value (NPF) Nominal Pr	otection Factor		

STORAGE

SHELF-LIFE

TEMPERATURE

RELATIVE HUMIDITY 70% max

TRANSPORT

MODEL	SIZE	CODE	WEIGHT (g)	Q.TY / BOX	Q.TY / CARTON	CARTON WEIGHT (Kg)
SGE46	One size fits all	8002059	150	1	8	1,28

CERTIFICATION

BLS respirators are:

• certified according with the European Regulation 425/2016 (Personal protective equipments)

• certified as PPE of III category, in presumption of conformity to harmonized standard EN 140:1998

• certified and controlled according to Annex D by Italcert S.r.l. (Notified Body n°0426)

CE marked

BLS management system is ISO 9001:2008 certified



10 years / 5 years (thermoplastic)

 $-10^{\circ}/+50^{\circ}$ C





R 19/09/19





MADE IN ITALY



AVAILABLE MODELS

COMPATIBLE DEVICES

RESPIRATORY

PROTECTION

PRODUCTS

DEVICES WITH THE SAME CONNECTION



Half maks BLS SGE46



FIIters SERIE BLS 400



Full face masks BLS 5400 - BLS 5150



Full face masks BLS 3400 - BLS 3150 (V)

SELECTION GUIDE

HALF MASK VS DISPOSABLE MASK

- Easier to wear properly
- Can be used with anti-gas filters
- HALF MASK VS FULL FACE MASK
- · Less invasive, better supports intermittent use

IMPORTANT

BLS declines any responsibility, direct or indirect, from any misuse of both devices and instructions. User is responsible for the determination of product compliance with the intended use.